

Refraction was measured with Plusoptix.
 Check out our range of binocular autorefractors for your clinic.
www.plusoptix.com







Certifikát

Jakub Novotny, 2016-03-06


Datum měření: 2020-11-02

OD

OS



Refrakce	[dpt]
-0,75 0,00 n/a° +0,25 -0,25 89°	
Odchylka pohledu	[°]
2,1	
Průměr zornice	[mm]
3,8 4,1	
Vzdálenost zornic	[mm]
66	
Úklon hlavy	[°]
0	



Ver. 7.1.8.0

Refraction was measured with Plusoptix.
 Check out our range of binocular autorefractors for your clinic.
www.plusoptix.com

